




KENDA MAXIMUS

1-STEP DIAMOND POLISHING SYSTEM

- Extremely efficient and time saving polishing on all composites
- From a scratched surface to an ultra luster in only one step
- High diamond content
- No paste for high shine polishing needed
- Optimized for Microhybrids and Nanofills



«This polisher has tested to give a significant better shine and finer surface.»



SET REF 0380.006A

12



REF reorder	0385	0386	0388	0389	0390	0391
ISO 1: 828 204	030 493 060	243 493 030	243 493 050	303 493 100	030 493 090	030 493 060
$\varnothing \times L$ mm	6.5 x 10	3 x 7	5 x 10	10 x 1	9 x 8.5	6 x 7.5
μ grit	ultra-fine		color		rec.	max.
	ultra-fine		light beige		5000 - 7500 RPM	10.000 RPM
Refill Box of:	N Pressure:		Autoclavable:	Shank:	Medical device:	
6, 12, 25, 100	0,3 - 2N		135°C, 275°F	RA, stainless steel	Class IIa	

