




*Track<sup>®</sup>*  
*Thermoforming foils*




# TRACK® Thermoforming foils



**Fast processing due to integrated separating foil!**  
Track® A and B cut down on several processing steps: the use of separating liquid or a separating foil and manual preparation is not required because Track® A and B have an integrated separating foil.



**No bond enhancing agent required!**  
Track® A and Track® B thermoforming foils do not require bond enhancing medium to bond to acrylic (Forestacryl).



**Superior thermobonding characteristics!**  
Better thermobonding when separately processed parts of an appliance are joint together i.e. snoring appliances and positioners. The improved performance during thermobonding reflects the use of superior materials in the manufacturing process of Track® E.

ø 125 mm, transparent

Order No.	Thickness	Content		Description	Application	Bonding to acrylic
408-0105	0.5 mm	100		<b>Track® A</b> hard (PETG)	Bite, bruxism* and stabilisation splints, correction splints (aligner), anti-snoring splints  * for fabrication of bruxism splint only foils with a thickness of ≥ 1.0 mm may be used	yes
408-0106	0.6 mm	100				
408-0108	0.8 mm	100				
408-0110	1.0 mm	100				
408-0115	1.5 mm	50				
408-0120	2.0 mm	50				
408-0220	2.0 mm	30		<b>Track® B</b> Double layer (TPU/PET-G)	Bite, bruxism, correction splints (aligner), anti-snoring splints	yes (on hard side)
408-0305	0.5 mm	100		<b>Track® C</b> soft (PE)	Placeholder for drug carrier / bleaching trays in combination with a hard splint	no
408-0310	1.0 mm	100			Inner layer of transfer splints, in combination with hard splint	
408-0515	1.5 mm	50		<b>Track® E</b> soft, rubbery (EVA)	Soft splint, Inner layer of bracket transfer splints, in combination with hard splint	no
408-0520	2.0 mm	50			Positioners, soft splints, bracket protection splints	
408-0530	3.0 mm	30				
408-0610	1.0 mm	100		<b>Track® bleach</b> (EVA)	Bleaching and fluoridation trays, in combination with placeholder foil	no















# TRACK<sup>®</sup>-V vacuum Thermoforming unit

Order No.		Content	Description
900-2000		1	<b>Track<sup>®</sup>-V</b> Vacuum thermoforming unit, 230 V
900-2110		1	<b>Track<sup>®</sup>-V</b> Vacuum thermoforming unit, 100 V, Japan
900-2115		1	<b>Track<sup>®</sup>-V</b> Vacuum thermoforming unit, 115 V, USA






# TRACK<sup>®</sup>-P and TRACK<sup>®</sup>-P-ci – Pressure thermoforming unit (with / without integrated compressor)

Order No.		Content	Description
900-2300		1	<b>Track<sup>®</sup>-P</b> Pressure thermoforming unit, 230 V
900-2310		1	<b>Track<sup>®</sup>-P</b> Pressure thermoforming unit, 100 V, Japan
900-2315		1	<b>Track<sup>®</sup>-P</b> Pressure thermoforming unit, 115 V, USA
900-2400		1	<b>Track<sup>®</sup>-P-ci with integrated compressor</b> Pressure thermoforming unit, 230 V
900-2410		1	<b>Track<sup>®</sup>-P-ci with integrated compressor</b> Pressure thermoforming unit, 100 V, Japan
900-2415		1	<b>Track<sup>®</sup>-P-ci with integrated compressor</b> Pressure thermoforming unit, 115 V, USA

## TRACK®-V – Auxiliaries

Order No.	Description		Content
408-0705	<b>Cover template</b> , ø 0.5 x 100 mm (8 pcs)		1
408-0706	<b>Occluform for Track®-V</b>		1
900-2001	<b>Filling granules</b> , refill package, 1.3 kg		1
900-2002	<b>Blocking out plaster</b> , 400 g		1
900-2003	<b>Blocking out wax</b> , transparent, 50 g		1
900-2012	<b>Brush for granules</b> , incl. magnet		1
900-2016	<b>Sealing for foil reception</b>		1
900-2017	<b>Sealing for form pot</b>		1
900-2018	<b>Finishing set Track®</b> for cutting and finishing Track® foils		1
900-2006	<b>Power supply cable for Track®-V</b>		1
900-2007	<b>Foil securing ring</b> to fix the foils in the foil reception		1
900-2008	<b>Filling granules collecting container</b>		1
900-2010	<b>Model plate</b>		1
900-2011	<b>Granules pot</b>		1

## TRACK®-P and TRACK®-P-ci – Auxiliaries

Order No.	Description		Content
900-2301	<b>Foil securing ring</b>		1
900-2302	<b>Foil holder</b>		1
900-2303	<b>Form pot</b>		1
900-2304	<b>Brush for filling granules with rubber cap</b>		1
900-2305	<b>Filling granules</b> , 1.3 kg		1